

## Crete Rx™ Honing Tool (3/case)



Crete Rx™ Honing Tool (3/case)

### Features

Use with LiquiGrind to grind out imperfections in previously polished concrete  
Prepares concrete for polishing step by removing imperfections and smoothing surface

### Available In

**Crete Rx™ Honing Tool (3/case) Item #E84133-00**

### Directions for Use

Please refer to the Betco Crete Rx Procedures document for full procedure. Attach the Betco Crete Rx Honing Tool to proper equipment to be used either via Velcro or magnetic Tool Holders. Place equipment in LiquiGrind and begin initial grinding procedure. If using propane equipment, allow one pass at roughly 15 to 20 ft./minute. Overlap each pass by at least one quarter to ensure proper restoration pass. If using autoscrubber application, allow for eight to ten passes at the same rate. Be sure to keep concrete wet in this step.

### Tech Specs

Hone Autoscrubber	50000 sq.ft.
Hone CP30	5000 sq.ft.
Weight	130 grams
Color	Light Brown